

Ninox 640 SU

High resolution, low noise, Deep cooled, digital SWIR camera
640 x 512 • 15 μ m x 15 μ m Pixel Pitch • Cooled to -80°C • <40e- in high gain •



Key Features and Benefits

The best performing SWIR camera in the World!

- **Vacuum cooled to -80°C**
Enables ultra-long exposure times
- **Ultra-low dark current and read-noise**
Resulting in the highest sensitivity SWIR camera on the market
- **15 μ m x 15 μ m pixel pitch**
Enables highest spatial resolution
- **PentaVac Vacuum Technology**
Guaranteed protection and integrity of sensor

Resolution	640 x 512
Frame Rate	Up to 98Hz
Camera Link	16 bit
Wavelength Range	SWIR
Dark Current	<300 e/p/s

PRELIMINARY

Specification for Ninox 640 SU

Sensor Type	InGaAs PIN-Photodiode
Active Pixel	640 x 512
Pixel Pitch	15µm x 15µm
Active Area	9.6mm x 7.68mm
Spectral response ¹	0.9µm to 1.7µm
Readout Noise (RMS) LG = Low Gain HG = High Gain	HG: <40e- (Typical <33e-) LG: <96e- (Typical <92e-)
Peak Quantum Efficiency	80% @ 1.5µm
Full Well Capacity	Low Gain: >85ke-, High Gain: >18.5ke-
Pixel Operability	>99%
Dark Current (e/p/s)	<300 @ -80°C
Digital Output Format	16 bit CameraLink (Base configuration) / SDR
Exposure time	20µs - 300 secs *
Shutter mode	Global shutter
Frame Rate	98Hz
Dynamic Range (typical)	Low Gain: 59.6dB High Gain: 56dB
Optical Interface	C-mount (selection of SWIR lens available)
Camera Setup / Control	16 bit Camera Link (Base Configuration / SDR)
Trigger interface	Trigger IN and OUT - TTL compatible
Power supply	12V DC ±10%
TE Cooling	-80°C with liquid cooling
Image Correction	2 Point NUC (Offset & Gain) + pixel correction
Functions controlled by serial communication	Exposure, Non Uniformity Correction, TEC
Camera Power Consumption ²	<120W (TEC ON, NUC ON)
Operating Case Temperature ³	-20°C to +55°C
Storage Temperature	-30°C to +60°C
Dimensions (L*W*H) ⁴	120.9mm x 140.2mm x 113.1mm
Weight	<1.9kg

Raptor Photonics Limited reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.
* IN HG mode exposure will be limited due to pixel well depth.

Ordering Information

Camera

Ninox 640 SU Digital Camera	NXU1.7-CL-640
Ninox Power Supply Cable	RPL-NXU-PSU

Optional Accessories


Mini PC with XCAP STD and frame grabber	RPL-PC-mf2280
Thunderbolt frame grabber	RPL-mf2280
EPIX® EB1 frame grabber	RPL-EPIX-EB1
EPIX® XCAP Std software	RPL-XCAP-STD
MDR-SDR CameraLink Cable (2m) ⁵	RPL-MCL-CBL-2M
Chiller Tubing ⁶	RPL-WTUBE-NINOX
Thermoelectric Water Chiller Unit	RPL-CHILLER
Optical SWIR lenses ⁷	RPL-xx-xxxx

- Note 1: Optional filters available.
- Note 2: Measured in an ambient of 25°C with adequate heat sinking.
- Note 3: Extended operating temperature range on request.
- Note 4: Dimensions include all connector parts on camera interface.
- Note 5: Longer Camera Link cable available.
- Note 6: This includes the tubing & connectors.
- Note 7: Please consult us to check our range of lenses.

Demo is available on request.
Pricing AOR subject to volumes.

Detailed technical drawings can be downloaded at www.raptorphotonics.com

Quantum Efficiency



* Data supplied by sensor manufacturer.

Applications

Scientific

- Art Inspection
- Astronomy
- Beam Profiling
- Hyperspectral Imaging
- In-vivo / NIR-II imaging
- Microscopy
- Semiconductor Inspection
- Solar Cell Inspection
- Thermography



Willowbank Business Park
Larne, Co Antrim
BT40 2SF,
Northern Ireland

Raptor Photonics Ltd. (UK)
T: +44(0)2828 270 141
E: sales@raptorphotonics.com
www.raptorphotonics.com

Raptor Photonics Inc. (USA)
T: +1 (877) 230-4836
E: sales@raptorphotonics.com
www.raptorphotonics.com

Document #: USNXU1.7-CL-640 0322

