

Uniblitz® VCM-D1

Single-Channel Uni-Stable Shutter Controller



Overview

For nearly 15 years, the Uniblitz VCM-D1 has been providing high-performance shutter control. This single-channel, uni-stable driver is versatile and proven, and it's compatible with many Uniblitz shutters. In addition to direct shutter control via the BNC inputs, shutters can also be controlled via RS-232C computer serial ports, allowing up to 8 separate driver units to be daisy-chained (810RJ cables required).

See the [VCM-D1 User Manual](#) for additional information regarding this device. The VCM-D1 is **RoHS compliant** and **CE certified**.

Need Support? Please [visit our website](#) or email us at info@uniblitz.com.

Tel: 585-385-5930 | Toll-Free: 800-828-6972 | Fax: 585-385-6004 | 803 Linden Ave. Rochester, NY 14625

Updated 11/22 | Datasheet Version 5.1 | ©2022 Vincent Associates

What's Included

- VCM-D1 Shutter Driver
- Manual (included on flash drive)
- **710A** Cable (3.0 m)
- **501A-S7** Adapter Cable (17.8 cm)
- Line Cords (USA and Euro)
- Fuses (2) (0.25 AMP S-B)
- Key Switch Keys (2)

Shutter Compatibility

CS	DSS	LS	NS	TS	VS	XRS
CS25		LS2			VS14	XRS6
CS35		LS3			VS25	XRS14
CS45		LS6			VS35	XRS25 ¹
CS65						
CS90						

Use with shutter devices other than those listed to the left is not recommended. Please contact us for further information.

¹ Will require two drivers for operation.

Operation Modes

STD - Standard shutter operation:

Exposure is determined by an external pulse source or switch contact closure.


A - Line interrupt mode:

When a loss of line power is detected, the VCM-D1 powers down. When power is restored, it must be manually or remotely reset to resume standard operation.

B - DC interrupt:


Detects a break in external switch contact. When continuity is restored, it must be manually or remotely reset to resume standard operation.

Device Layout



Front Panel

LED indicators reveal shutter status at a glance, while the MODE key switch will set the unit to a specific interrupt mode not allowing an inadvertent change in setting once the key is removed. Additional interrupt functions are available at the MODE CONTROL 7-PIN pluggable connector. The AUX out-put and +5 VDC output are also available at the MODE CONTROL connector.



Rear Panel

All main input/output functions can be accessed at the VCM-D1 rear panel, including the 115/230VAC input which is manually selectable. BNC connectors allow for quick termination of TTL command signals. Function switches A-F determine the active state of the BNC inputs or outputs (high or low level active). Function switch H selects HIGH/LOW energy level. Function switch G will disable the SYNC output BNC and disable the IR emitter of the synchronization circuit within the shutter used.

Technical Specifications

Size (H x W x D)	Weight
2.73 x 5.41 x 8.18 inches (69.3 x 137.4 x 207.8 mm)	3.5 lbs (1.59 kg)

Power
115 / 230 VAC, 50 - 60 Hz, 60 W

Product Options

VCM-D1 ²	Ex: VCM-D1J
<p>¹ Driver:</p> <ul style="list-style-type: none">• VCM-D1	<p>² Japan Modification:</p> <ul style="list-style-type: none">• J: Included• Leave blank if not required