

# Water-Cooled Thermopile Sensors to 5 kW

## Compact, USB Water-Cooled Laser Power Sensors

These compact sensors are particularly useful when space is an issue. They must be water-cooled to achieve the full power rating, and they can also be used air-cooled (stand-alone or mounted to a heat sink) for stand-alone intermittent application of power.

#### **FEATURES**

- Compact designs
- Use water-cooled or air-cooled
- 19 mm and 50 mm apertures

#### **APPLICATIONS**

- Medical
- Scientific
- Industrial
- General Laser Power Measurement to 5 kW






SPECIFICATIONS	PM10-19C	PM100-19C	PM150-19C	PM150-50C
Wavelength Range (µm)	0.19 to 11			
Power Range (water-cooled)	10 mW to 10 W	300 mW to 100 W	300 mW to 150 W	300 mW to 150 W
Maximum Intermittent Power (W) (<5 min.)	5 (air-cooled)	100	20 (air-cooled)	80 (air-cooled)
Long-Pulse Joules (J)	0.5 to 10	1 to 100	1 to 150	1 to 150
Noise Equivalent Power (mW)	0.2	1	1	1
Maximum Power Density (kW/cm <sup>2</sup> )	6			
Maximum Energy Density (mJ/cm <sup>2</sup> )	600 (10 ns , 1064 nm)			
Response Time (sec.) (0% to 95%) Speed-up On Speed-up Off	2 4	2 4	2 4	3 12
Detector Coating	Broadband			
Detector Element	Thermopile			
Optic	None			
Detector Diameter (mm)	19	19	19	50
Calibration Uncertainty (%) (k=2)	±2			
Power Linearity (%)	±1			
Spectral Compensation Accuracy (%)	±1.5			
Long-Pulse Joules Accuracy (%)	±3			
Calibration Wavelength (nm)	10,600			
Cooling Method	Water/Air (intermittent)			
Cable Type	USB and RS			
Cable Length (m)	2.5 (USB)/0.3 (RS)			
Part Number USB RS-232	1168344 1168345	1288940	1168346 11683471	1168348 <sup>1</sup> 1168349 <sup>1</sup>

1 1 Day Ship program: eligible for next business day shipment.


### MECHANICAL SPECIFICATIONS

#### PM10-19C/PM150-19C


(shown with PowerMax-RS cable)



PM150-50C (shown with PowerMax-RS cable)



PM100-19C







SPECIFICATIONS	PM150-50XC	PM1KX-100	PM5K-100		
Wavelength Range (µm)	0.15 to 1	0.15 to 1	0.25 to 10.6		
Power Range	300 mW to 150 W	50 W to 1000 W	100 W to 5000 W		
Noise Equivalent Power (mW)	1	20	20		
Maximum Power Density <sup>1</sup> (kW/cm <sup>2</sup> )	6	1 to 2.5	1 to 2.5		
Maximum Energy Density (mJ/cm <sup>2</sup> )	600				
Response Time (sec.) (0% to 95%) Speed-up On Speed-up Off	3 12	4 6	4 12		
Detector Coating	UV	UV	Broadband		
Detector Element	Thermopile				
Detector Diameter (mm)	50	100	100		
Calibration Uncertainty (%) (k=2)	±2	±3	±5		
Power Linearity (%)	±1				
Spectral Compensation Accuracy (%)	±1.5				
Calibration Wavelength (nm)	524	1070	1070		
Cooling Method	Water				
Cable Type	USB and RS				
Cable Length (m)	2.5 (USB)/0.3 (RS)				
Part Number² USB RS-232	- 1305568	- 1214871	1235755		

1 The damage resistance of the coating is dependent upon the beam size and profile, the average power level, and the water flow rate. Contact Coherent or you local representative for details related to your application. 2 Software, water fittings and post stand included.

### **MECHANICAL SPECIFICATIONS**



PM1KX-100/PM5K-100



## 

Coherent, Inc., 5100 Patrick Henry Drive Santa Clara, CA 95054 p. (800) 527-3786 | (408) 764-4983 f. (408) 764-4646

#### tech.sales@coherent.com www.coherent.com

Coherent follows a policy of continuous product improvement. Specifications are subject to change without notice. Coherent's scientific and industrial lasers are certified to comply with the Federal Regulations (21 CFR Subchapter J) as administered by the Center for Devices and Radiological Health on all systems ordered for shipment after August 2, 1976.

Coherent offers a limited warranty for all Thermopile Sensors. For full details of this warranty coverage, please refer to the Service section at www.coherent.com or contact your local Sales or Service Representative. MC-013-21-0M0621 Copyright ©2021 Coherent, Inc.